Part Number : 1301540052
Product Description : Watertite Extreme Standard Molded Y Cordset, 2 Pole/3 Wire, Cordset Length 0.91m (3.0'), NEMA 6-20, 250V
Series Number : 130154
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 14W48-Y



Documents and Resources

Drawings

1301540052_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Wiring Devices
Series	130154
Description	Watertite Extreme Standard Molded Y Cordset, 2 Pole/3 Wire, Cordset Length 0.91m (3.0'), NEMA 6-20, 250V
IP Rating	IP69K
NEMA Configuration	NEMA 6-20
Product Name	Watertite Extreme
Specialty	N/A
Type	Molded Y Cordset
UPC	78678800610

Agency

CSA	LL52750

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Grip Body Size	F2 1/2"
Cord Type	12/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	0.91m (3.0')
Lighted Connector	No
Locking Blade	No
Poles	2-pole/3-wire
Receptacle Type	Duplex

Downloaded from Arrow.com.

Downloaded from Arrow.com.