Specifications



Photo is representative





Eaton UP1B-101-R

Eaton UP inductor, Inductance 100.0 µ H, 0.47 A Irms, 0.53 A Isat, 1.11 Ω DCR

General specifications	
PRODUCT NAME	Eaton UP1B inductor
CATALOG NUMBER	UP1B-101-R
UPC	051712894388
EAN	5027590117845
PRODUCT LENGTH/DEPTH	0.35 in
PRODUCT HEIGHT	0.197 in
PRODUCT WIDTH	0.24 in
PRODUCT WEIGHT	0.00084 lb
COMPLIANCES	RoHS Compliant
GLOBAL CATALOG	UP1B-101-R
PRODUCT TYPE	Inductor

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	0.47 A
ISAT	0.53 A
PACKAGE QUANTITY	900
MATERIAL	Ferrite
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	1100 mΩ
SERIES	UP1B

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UP1B-101-R

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.