



+ RELAYS, CONTACTORS & SWITCHES

TIME DELAY RELAYS



✓ Active

TE CONNECTIVITY (TE)
7022BDX=RLY,STD,OFF,2P,240VAC

Agastat | 7000 Electropneumatic Timing - Industrial

7022BDX
TE Internal Number: 2-1423162-5

Not EU RoHS Compliant
Not EU ELV Compliant

Type of Control Knob
Input Voltage (VAC) 220, 240
Timing Range (Off-Time) (seconds) 5 – 50
Mode of Operation Off-Delay
Delay Time 5 – 50 seconds

DOCUMENTATION

Catalog Pages/Data Sheets
5-1773450-5_sec12_7000
PDF
English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features
Product Category Electromechanical Relays
Relay Type Time Delay
Product Type Relay

Configuration Features

Multiple Timing Ranges Without

Electrical Characteristics

Input Voltage (VAC) 220, 240
Timing Range (Off-Time) (seconds) 5 – 50
Actuating System AC

Contact Features

Type of Control Knob
Delay Time 5 – 50 seconds
Contact Arrangement 2 Form C, DPDT, 2 C/O

Termination Features

Termination Type Screw Terminals

Mechanical Attachment

Mounting Type Panel Mount

Dimensions

Dimensions (L x W x H) (Approximate) 114.8 x 65.3 x 71.9 mm [4.523 x 2.572 x 2.832 in]

Usage Conditions

Operating Temperature Range (°C) -30 – 75

Operation/Application

Mode of Operation Off-Delay
Option Hardware and Adjustment for Horizontal Operation

Other

Repeatability (Max) ±5%

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF