



Part Number : [190980074](#)

Product Description : Krimptite Snap Spade Terminal, for 10-12 AWG Wire, Stud Size 10 (M5), 19.60mm Length

Series Number : 19098

Status : Active

Product Category : Ring and Spade Terminals

Engineering Number : C-1719-10

Documents & Resources

Drawings

[Drawing 190980074_sd.pdf](#)

3D Models and Design Files

[3D Model 190980074_stp.zip](#)


Specifications

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19098
Description	Krimptite Snap Spade Terminal, for 10-12 AWG Wire, Stud Size 10 (M5), 19.60mm Length
Keyword	Spade Terminal, Spade Terminals
Product Family	Solderless Terminals
Product Name	Krimptite
Type	Spade Snap
UPC	800755081596

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	1.282/g
Packaging Type	Bag
Stud Size	10 (M5)
Wire Size (AWG)	10, 12
Wire Size mm ²	3.30-5.00

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm ² - 0.5mm ²	<u>640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>

This document was generated on Jul 28, 2024