

YAV10T23F

by Burndy
Catalog ID: YAV10T23F

Copper Uninsulated Compression Lug, Heavy Duty, Fork Tongue, 12-10 AWG, 1/4" Stud, Tin Plated



Product Details

General

Connector Type	Terminal - Fork
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Fork Tongue
UPC	781810025390

Dimensions

Dimension - B Length fraction	2/5 in
Dimension - B Length inch	0.41 in
Dimension - D inch	0.59 in
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.03 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.22 in
Dimension - Pad Width inch	0.47 in
Dimension - Strip Length inch	7/16 in
Dimension - Stud Size inch	1/4 in
Dimension - Z inch	0.34 in

Conductor Related

Conductor - Copper Str Aircraft Size	AN 12;AN 10
Conductor - Copper Str Aircraft Size Range	AN 12-AN 10
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)