

**TIGER™
EYE
SYSTEM**



MH-130-02-L-D-LC



HIGH-RELIABLE HORIZONTAL

RV[®]
FILE NO. E111594

**TIGER™
EYE**

Technical drawing of a mechanical part with dimensions and tolerances:

- Top dimension: $(0.64) \text{ .025 TYP}$ with a tolerance arrow pointing to the right.
- Left side dimensions: $(4.57) \text{ .180}$ with a tolerance arrow pointing to the left.
- Right side dimensions: $(1.65) \text{ .065}$ with a tolerance arrow pointing to the right.
- Bottom dimension: $(2.03) \text{ .080}$ with a tolerance arrow pointing to the left.

-FR
= Full Reel Tape & Reel
(must order max. quantity
per reel; contact Samtec
for quantity breaks)

HORIZONTAL

Downloaded from Arrow.com.