

Part Number : [510150600](#)

Product Description : 2.00mm Pitch, Board-In Crimp Housing, Vertical, 6 Circuits, Natural

Series Number : 51015

Status : Active

Product Category : Connector Housings



Documents and Resources

Drawings

[510150600_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[510159200-SPK-200.pdf](#)

[510151002-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	51015
Description	2.00mm Pitch, Board-In Crimp Housing, Vertical, 6 Circuits, Natural
Application	Signal, Wire-to-Board
Product Name	Board-in
UPC	800753575769

Physical

Circuits (maximum)	6
Color - Resin	Natural
Gender	N/A
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	114.500/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No

Temperature Range - Operating	-40° to +105°C
-------------------------------	----------------

Mates With / Use With

Use with Part(s)

Description	Part Number
2.00mm Pitch Board-in Vertical Male Crimp Terminals	<u>50034</u>

This document was generated on Apr 12, 2026