Part Number : 731714360
Product Description : BNC Jack, Right-Angle, Bulkhead Receptacle, PCB, Through Hole, Die Cast Body, Nickel (Ni) Plated, Housing Height 15.59mm, One Piece per Bag, 50 Ohms
Series Number : 73171
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

731714360_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73171
Description	BNC Jack, Right-Angle, Bulkhead Receptacle, PCB, Through Hole, Die Cast Body, Nickel (Ni) Plated, Housing Height 15.59mm, One Piece per Bag, 50 Ohms
Application	RF
Comments	15.59mm Profile
Product Name	BNC
Style	PCB
Type	Miniature
UPC	884982944367

Electrical

Frequency	2 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Orientation	Right Angle
Packaging Type	Individual Bag
Panel Mount	Yes
Panel Mount Method	Bulkhead

Downloaded from Arrow.com.

PCB Mounting	Through Hole
PCB Thickness - Recommended	3.20mm
Reverse Polar	No
Wire/Cable Type	N/A

Downloaded from Arrow.com.