


Connector Location A





Connector Location B



X

Y

Loading-Plan
acc. to TIA/EIA 568B



- Protection level: IP67
- Temperature range: -20°C ... +70°C

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
	All rights reserved	Created by COSTEA	Inspected by COSTEA	Standardisation MUNTEANV	Date 2017-12-11	State Final Release	
	Department HCS - RO	Title Han 3A RJ45 Hybrid Cable Assembly				Doc-Key / ECM-Nr. 100174924/UGD/006/F 500000128829	
HARTING Customised Solutions D-32339 Espelkamp		Type TB	Number 094572515XX			Rev. F	Page 1/2

	1	2	3	4	5	6	7	8
A								
B								
C								
D								
E								
F								
	21	09457251518	Hybrid cable 4x2xAWG26/7 + 4x1.5mm², PUR, Cat.6, black	60				
	20	09457251517		50				
	19	09457251516		40				
	18	09457251515		30				
	17	09457251521		25				
	16	09457251514		20				
	15	09457251513		15				
	14	09457251519		12				
	13	09457251512		10				
	12	09457251511		9				
	11	09457251510		8				
	10	09457251509		7				
	9	09457251508		6				
	8	09457251507		5				
	7	09457251506		4				
	6	09457251520		3.5				
	5	09457251505		3				
	4	09457251504		2				
	3	09457251503		1.5				
	2	09457251502		1				
	1	09457251501		0.5				
	Cont. no.	Part no.	Type of cable	Dim. a[m]				
	1							
	2							
	3							
	4							
	5							
	6							
	7							
	8							



All rights reserved

Department HCS - RO

Created by

COSTEA

Inspected by

COSTEA

Standardisation

MUNTEANV

Date

2017-12-11

State

Final Release

Title

Han 3A RJ45 Hybrid Cable Assembly

Type

TB

Number

094572515XX

Doc-Key / ECM-Nr.

100174924/UGD/006/F
500000128829

Rev.

F

Page

2/2

All Dimensions
in mm

Tech. Character.

Free size tol.

According to production drawing

HARTING Customised Solutions

D-32339 Espelkamp