

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search


Multi Selection Search

Search by category

Start > Search=VR05515100J0G* > VR05515100J0G

VR05515100J0G

VR05515100J0G - Terminal Blocks : Pluggable plug, 5.08mm pitch, upside contact, horizontal wire-inlet, 5 position



ACTIVE

Distributor Stock

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Customer drawing

Environmental Compliance Report

Specifications

Download document

Mating Half

Dimensional	General	Electrical	Mechanical	Physical	Approvals / Certifications
Dimensional					
Strip length (Wire)	7 to 8 mm				
Solid wire size (AWG)	14 to 30				
Stranded wire size (AWG)	14 to 30				
Pitch	5.08 mm				
Screw Size	M2				
General					
Gender	Female plug				
Packaging	Box				
Product Type	Screw Pluggable System				
Series	VR				
Number of Positions	5				
Electrical					
Withstanding Voltage	1.6 kV				
Current rating	10 A				
Voltage rating	300 V				
Mechanical					
Number of mating cycles	200				
Physical					
Color (Housing)	Green				
Conductor entry angle	0°				
Material (Housing)	Thermoplastic UL94V-0				
Terminal material	Phosphor bronze				
Terminal plating	Tin				
Screw material	Steel				
Screw plating	Zinc				
Clamp material	Brass				
Clamp plating	Nickel				
Connection Type	Screw connection				
Temperature (Operating - range)	-40 to 115 Celcius				
Torque	2 Lb-in				
Approvals / Certifications					
Approvals / Certifications	cULus				

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.

Downloaded from Arrow.com.