



Part Number : [2025693005](#)

Product Description : Ultra-Fit Plug Housing,
3.50mm Pitch, Single Row, 5 Circuits, Black, Glow-Wire
Capable

Series Number : 202569

Status : Active

Product Category : Connector Housings



Documents and Resources

Drawings

[2025693005_sd.pdf](#)

[2025691000-PK-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[1723230003-000.pdf](#)

[2169461000-PS-000.pdf](#)

[2169460001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2- diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	202569
Description	Ultra-Fit Plug Housing, 3.50mm Pitch, Single Row, 5 Circuits, Black, Glow-Wire Capable
Application	Power, Wire-to-Wire
Product Name	Ultra-Fit
UPC	195842150683

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	5
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	Yes

Lock to Mating Part	Yes
Material - Resin	Polyamide
Net Weight	1.790/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C, -40° to +120°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Ultra-Fit Tangless Receptacle Housing, 3.50mm Pitch, Single Row, 5 Circuits, Black, Glow-Wire Capable	<u>1722563105</u>

Use with Part(s)

Description	Part Number
Ultra-Fit Tangless Terminal Position Assurance (TPA), 3.50mm Pitch, 5 Circuits, Natural	<u>1722644005</u>
Ultra-Fit Male Crimp Terminals	<u>216946</u>

This document was generated on Apr 15, 2026