


REV	ECN	APP'D
-	5938	<i>[Signature]</i>



NOTES:




1. MATERIALS:

HOUSING: POLYETHERIMIDE, COLOR BLACK
 GROMMET: SILICONE ELASTOMER, COLOR BLUE
 INTERNAL CONTACT: COPPER ALLOY, GOLD PLATED,
 PER MIL-G-45204, TYPE I, GRADE C, CLASS I.
 CONTACT RETAINER: STAINLESS STEEL

2. SPLICE ACCEPTS (2) MATING M39029/1-101 CONTACTS
 (NOT INCLUDED)

3. PART COMPLIES TO ALL REQUIREMENTS PER MIL-T-81714.

4. RESISTOR: 10K Ω , 1/8W

DIMENSIONS ANSI Y14.5M UNITS: INCHES Pro/E FILE	TOLERANCES .XX ±0.01 .XXX ±0.005 ANGLES ±2.0°	PROJECTION 	Amphenol Pcd SPECIFICATION DRAWING ENGR D. LANG03/08/06		TITLE WIRE SPLICE, ELECTRONIC RESISTOR, 10K Ω, 1/8W SIZE 20			
	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC., PEABODY, MA			CHKD 	SIZE A	DWG NO. TJSE20525_C	REV -	
				APPD 	CODE: 58982	SCALE: 2:1	SHEET 1 OF 1	