


REV.	DATE	ECR NO.	DESCRIPTION
NC	10/09/30	XXXXXX	INITIAL RELEASE



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING					APPROVALS		DATE		Amphenol Connex PART DESCRIPTION N PANEL RECEPT. JACK										
					DRAWN		T.DENG						10/09/30						
					CHECKED														
					ISSUED				PART NO.										
					SHEET		1 OF 1												
					172361-10														
					CAD FILE				DWG. NO.		172361-10.DWG		REV.	A	SIZE	A	SCALE	NA	
					C:/CONNEX/172361-10.DWG														
3	CONTACT PIN	PHOSPHOR BRONZE	GOLD	1															
2	INSULATOR	PTFE	NATURAL	1															
1	BODY	BRASS	NEXCOTE	1															
DESCRIPTION		MATERIAL		FINISH	QTY														