



Pushing Performance
Since 1945

Han D F CRIMP CONTACT Fe(Au) 0,14-0,37



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 000 6271
Specification	Han D F CRIMP CONTACT Fe(Au) 0,14-0,37
HARTING eCatalogue	https://harting.com/09150006271

Identification

Category	Contacts
Series	Han D [®]
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.14 ... 0.37 mm ²
Conductor cross-section [AWG]	AWG 26 ... AWG 22
Rated current	≤10 A
Contact resistance	≤1 mΩ
Stripping length	8 mm

Material properties

Material (contacts)	Iron
Surface (contacts)	Gold plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	25
Net weight	0.4 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140022218
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522