

## Han-Eco 16B-HSE-for DL-M32



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 19 43 016 0527  |
| Specification      | Han-Eco 16B-HSE-for DL-M32  |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19430160527">https://b2b.harting.com/19430160527</a> |

### Identification

|                          |                |
|--------------------------|----------------|
| Category                 | Hoods/Housings |
| Series of hoods/housings | Han-Eco® B     |
| Type of hood/housing     | Hood           |

### Version

|              |                      |
|--------------|----------------------|
| Size         | 16 B                 |
| Version      | Side entry           |
| Cable entry  | 1x M32               |
| Locking type | Double locking lever |

### Technical characteristics

|  |  |
|--|--|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Number of relockings                   | ≥500   |
| Degree of protection acc. to IEC 60529 | IP66   |

### Material properties

|   |  |
|---|--|
| Material (hood/housing)                   | Polyamide (PA)<br>Fibre-glass reinforced |
| Colour (hood/housing)                     | RAL 9005 (jet black)                     |
| Material flammability class acc. to UL 94 | V-0                                      |
| RoHS                                      | compliant                                |
| ELV status                                | compliant                                |



Pushing Performance  
Since 1945

## Material properties

|                                      |                              |
|--------------------------------------|------------------------------|
| China RoHS                           | e                            |
| REACH Annex XVII substances          | Not contained                |
| REACH ANNEX XIV substances           | Not contained                |
| REACH SVHC substances                | Not contained                |
| California Proposition 65 substances | Yes                          |
| California Proposition 65 substances | Naphthalene                  |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08)         |
| Requirement set with Hazard Levels   | R22 (HL 1-3)<br>R23 (HL 1-3) |

## Specifications and approvals

|                |   |
|----------------|---|
| Specifications | IEC 61984<br>EN 45545-2 Fire protection on railway vehicles |
| Approvals      | CE  |

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 149 g                                    |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140178816                            |
| ETIM                           | EC000437                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |