

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

- Connector
- Size = Standard
- B Series
- Receptacle
- Without Locking Feature

1734091-1

TE Part Number: 1734091-1

Active

 Add to Part List

- USB CONN., RIGHT ANGLE, SHIELD, FLANGE, B TYPE (TIF, English)

- None Available

- None Available

- None Available

- None Available

- None Available

- Product Line Information

- Tooling

[List all Documents](#)

- Product Type = Connector
- Size = Standard
- Gender = Receptacle
- Number of Ports = 1
- Orientation = Right Angle
- PCB Thickness (mm [in]) = 1.57 [0.062]
- Number of Positions = 4

- Mount Location = Top

- Panel Ground Type = M2 Threaded Hole

- Termination Method = Solder to PC Board
- Tail Length (mm [in]) = 2.91 [0.115]

- Series = B
- Locking Feature = Without
- Panel Ground = With
- PCB Retention Method = Kinked Legs
- Shell Plating = Nickel over Copper
- Pick and Place Cover = Without
- Locating Posts = Without

- Contact Termination Type = Through Hole
- Contact Mating Area Plating Material = Gold
- Contact Mating Area Plating Thickness = 30 Microinches

- Housing Color = Black

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

- Terminate To = Printed Circuit Board

- Panel Ground Location = Top
- Packaging Method = Tray

- Brand = AMP