

Part Number : 1202540135
Product Description : Contrinex Photoelectric Sensor, M18 Plastic Housing, Background Suppression, 10 - 250mm Operating Distance, NPN, Changeover, Potentiometer Sensitivity Adjustment, 4-pin M12 Connector, 37mm Housing Length
Series Number : 120254
Status : Obsolete
Product Category : Inductive and Photoelectric Sensors
Engineering Part Number : LHR-M18PA-PMS-101

Obsolete

Documents and Resources

Specifications

1202540132-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Obsolete
Category	Photoelectric Sensors
Series	120254
Description	Contrinex Photoelectric Sensor, M18 Plastic Housing, Background Suppression, 10 - 250mm Operating Distance, NPN, Changeover, Potentiometer Sensitivity Adjustment, 4-pin M12 Connector, 37mm Housing Length
IP Rating	IP67
Operating Principle	Background Suppression
Product Name	Contrinex
Type	Photoelectric
UPC	191130068913

Electrical

Output	Changeover
Polarity	NPN
Switching Frequency	≤ 700 Hz

Physical

Connection	Connector (M12, 4-pin)
Length	37mm
Material - Housing	ABS
Material - Window	PMMA
Net Weight	99.000/g

Obsolete

Downloaded from Arrow.com.

Operating Distance	10 - 250mm
Output	Changeover
Sensor Housing Size	M18
Temperature Range - Operating	-25° to +55°C

Obsolete

Downloaded from Arrow.com.