

## SmartRack 3U Fan Panel - 3-120V high-performance fans; 210 CFM; 5-15P plug

MODEL NUMBER: SRFAN3U

### Highlights

- 3U Panel-mount Triple Fan Accessory



### Description

This SRFAN3U SmartRack® panel-mount Triple Fan Accessory (for use with SmartRacks) is ideal for increasing the ventilation of SmartRacks, enclosures and server cabinets. The unit features three four-inch 120V fans mounted in a 3U panel, six-foot (1.8-meter) cord and mounting hardware.

### Features

- SRFAN3U SmartRack Panel-mount Triple Fan Accessory (for use with SmartRacks) is ideal for increasing the ventilation of SmartRacks, enclosures and server cabinets
- The unit features (3) 4-in.-120V fans mounted in a 3U panel, 6-ft. (1.83 m) cord
- Includes mounting hardware

## Specifications

| OVERVIEW                           |                                |
|------------------------------------|--------------------------------|
| UPC Code                           | 037332144836                   |
| Accessory Type                     | Cooling Accessories; Fan Panel |
| Accessory Class                    | Cooling Accessories            |
| INPUT                              |                                |
| Nominal Input Voltage(s) Supported | 120V AC                        |
| Nominal Input Voltage Description  | 120V AC 50/60 Hz               |
| Input Connection Type              | NEMA 5-15P                     |
| Input Plug Features                | NEMA 5-15P                     |
| Voltage Compatibility (VAC)        | 120                            |
| Input Frequency                    | 50/60 Hz                       |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                         |
|--------------------------------------|-------------------------|
| Input Cord Length (ft.)              | 6                       |
| Input Cord Length (m)                | 1.83                    |
| <b>OUTPUT</b>                        |                         |
| Frequency Compatibility              | 50 / 60 Hz              |
| <b>COOLING</b>                       |                         |
| Cooling Type                         | Passive                 |
| <b>PHYSICAL</b>                      |                         |
| Rack Height                          | 3U                      |
| Shipping Dimensions (hwd / in.)      | 6.00 x 3.00 x 20.00     |
| Shipping Dimensions (hwd / cm)       | 15.24 x 7.62 x 50.80    |
| Shipping Weight (lbs.)               | 7.55                    |
| Shipping Weight (kg)                 | 3.42                    |
| Unit Dimensions (hwd / in.)          | 5.220 x 18.870 x 2.070  |
| Unit Dimensions (hwd / cm)           | 13.26 x 47.9 x 5.26     |
| Unit Weight (lbs.)                   | 5.5                     |
| Unit Weight (kg)                     | 2.49                    |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                         |
| Sound Level (Noise)                  | 45dB                    |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                         |
| Product Compliance                   | RoHS; EIA/ECA-310-E     |
| <b>WARRANTY &amp; SUPPORT</b>        |                         |
| Product Warranty Period (Worldwide)  | 2-year limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.