

Part Number : [191640056](#)

Product Description : Perma-Seal Butt Splice for 12-10 AWG Wire, Carton

Series Number : 19164

Status : Active

Product Category : Splices

Engineering Part Number : SC-12-10



Documents and Resources

Drawings

[191640056_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19164
Description	Perma-Seal Butt Splice for 12-10 AWG Wire, Carton
Product Name	Perma-Seal
Style	Standard
Type	Butt Splice
UPC	800753113411

Agency

CSA	LR18689
UL	E32244

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Yellow
Insulation	NiAc
Material - Metal	Copper
Material - Plating Mating	Tin

Material - Plating Termination	Tin
Net Weight	3.173/g
Packaging Type	Carton
Temperature Range - Operating	-55° to +125°C
Wire Insulation Diameter	7.87mm max.
Wire Size (AWG)	10, 12

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Industrial Terminals, 22-10 AWG (see ATS)	<u>640017400</u>
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	<u>640160041</u>

This document was generated on Apr 29, 2026