

[→ Honeywell.com](#) [→ Automation & Control Solutions](#)[HOME](#)[ABOUT US](#)[KEY INDUSTRIES SERVED](#)[PRODUCTS & INFORMATION](#)[NEWS & EVENTS](#)[SALES & SUPPORT](#)[LOGIN](#)

## Honeywell Sensing and Control

Search

**2450RG 80820923**

( Home : Products : Sensors » Thermostats » 2450RG )

### narrow your search

#### Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (5910)
- Switches (9781)
- Wireless (45)

#### Technology

- Electromechanical (9307)
- Magnetic (541)
- Microstructure (1495)
- Optical/Infrared (1042)
- Thick Film (1409)
- More...

### new products

#### New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site  
WGLA and WPMM  
XYR6000™

[find out more](#)

### white papers

Wireless Switches Offer  
Unlimited Benefit

Basic Switches Are Not Created  
Equal

Applying Precision Switches  
Sensors for Medical Devices

New Ways to Measure Torque  
Choosing Safety Switches

Specifying Hour Meters

### Need help?

[Click here to contact us](#)**2450RG Series Phenolic Automatic Reset Thermostats**

*Actual product appearance  
may vary.*

[Sales & Service](#)[Distributor Inventory](#)[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

#### Product Specifications

Functional Properties	Open on rise
Reset Type	Automatic
Amperage	0.5 A
Voltage	250 Vac/50 Vdc
Operating Temperature	0 °C to 150 °C [32 °F to 302 °F]
Environmental Exposure Range	-18 °C to 177 °C [0 °F to 350 °F]
Open Temperature	65.6 °C [150 °F]
Close Temperature	51.7 °C [125 °F]
Open Tolerance	2.8 °C [5 °F]
Close Tolerance	4.4 °C [8 °F]
Dielectric Strength	MIL-STD-202, Method 301; 2000 Vac 60 Hz - Terminal to Case
Insulation Resistance	MIL-STD-202, Method 302; Cond. B - 500 MOhm - 500 Vdc applied
Contact Resistance	MIL-STD-202, Method 307; 0.050 Ohm
Housing Material	Phenolic
Contact Material	WE -1 gold alloy cross point
Agency Approvals and Standards	UL, CSA
Mounting	B201 fixed bracket
Series Name	2450RG

### contacts

Customer Service  
Technical Support  
Global Sales & Service  
View Site Demo  
Site Comments?

### meet dr. larry

**VIDEO** - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

### my links

[Login to iCOM](#)  
[Login to Rep/AD Portal](#)  
[Login to Digital University](#)

### News Center

HONEYWELL INTRODUCES  
MICROPOWER OMNIPOLAR  
DIGITAL HALL-EFFECT  
SENSOR ICS WITH LOW  
SUPPLY VOLTAGE AND ULTRA  
LOW TYPICAL CURRENT

HONEYWELL EXTENDS ITS  
TRUSTABILITY® PRESSURE  
SENSOR PRODUCT LINE WITH  
A SINGLE SIDE LIQUID MEDIA  
OPTION

HONEYWELL ADDS NEW 100°  
AND 180° ARC  
CONFIGURATIONS TO ITS  
SMART POSITION SENSOR  
PORTFOLIO

HONEYWELL INTRODUCES  
ITS HAWK™ RESOLVERS 1-  
INCH SERIES, FULLY HOUSED  
CONFIGURATION

**MICRO SWITCH  
Anniversary site**

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)