

## Han TC200 Buchsenkontakt 35mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 6221
Specification	Han TC200 Buchsenkontakt 35mm <sup>2</sup>
HARTING eCatalogue	<a href="https://harting.com/09110006221">https://harting.com/09110006221</a>

### Identification

Category	Contacts
Series	TC 200
Type of contact	Crimp contact

### Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	35 mm <sup>2</sup>
Rated current	≤200 A
Contact resistance	≤0.3 mΩ
Stripping length	20 mm
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Vibration resistance	Category 2 acc. to IEC 61373
Shock resistance	Category 2 acc. to IEC 61373

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption



Pushing Performance  
Since 1945

## Material properties

RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	2
Net weight	28 g
Country of origin	Germany
European customs tariff number	85359000
GTIN	5713140015326
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522