

Search For

Home> 5680102173F

Part Number: **5680102173F**

General Description

Series	568
Configuration	3 mm Lens
Description	3 mm Quad-Level CBI G-R-O-Y
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Quad Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Diffused
Viewing Angle	60
LED Centerline	2.54mm

Absolute Maximum Ratings (Ta = 25°)

Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics

	LED Position: 1	LED Position: 2	LED Position: 3	LED Position: 4
Color	Green	Red	Orange	Yellow
LED Type	Standard Efficiency	Standard Efficiency	Standard Efficiency	Standard Efficiency
Peak Wave Length	565	635	600	585
Luminous Intensity Min	4.7	7.4	3.4	7.4
Luminous Intensity Typical	12.6	10	7	10
Forward Voltage Typical	2.1	2	1.9	2.1
Forward Voltage Max	2.8	2.8	2.4	2.8
Power Dissipation Max	100mW	100mW	135mW	60mW



5680102173F

[check stock](#)



This is a
RoHS Compliant Product

[To learn more click here](#)