A-INL-M25-P-LG - Counter nut

1417661

https://www.phoenixcontact.com/ae/products/1417661

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads M25 x 1.5, color: light gray



Commercial data

Item number	1417661
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AF7
Product key	AF7DZX
GTIN	4055626121642
Weight per piece (including packing)	3.59 g
Weight per piece (excluding packing)	3.184 g
Customs tariff number	39269097
Country of origin	TR


Downloaded from Arrow.com.

Technical data

Product properties

Product type	Flat nut
Thread type	M25

Dimensions

Dimensional drawing	
Length	6 mm
Diameter	25 mm
Connecting thread diameter	25 mm
Wrench size, counter nut	32 mm
Hexagon angular dimension	35 mm
Thread type connection side	M25 x 1.5
Thread pitch	1.5 mm

Material specifications

Material	PA 6.6 GF

Cable/line

Halogen-free	yes

Environmental and real-life conditions


Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C

Downloaded from Arrow.com.

Drawings

Dimensional drawing



Downloaded from Arrow.com.

Classifications

ECLASS

ECLASS-13.0	27140807
ECLASS-15.0	27140807

ETIM

ETIM 9.0	EC000879

UNSPSC

UNSPSC 21.0	31161700

Downloaded from Arrow.com.

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Middle East FZ LLC
1201N-1206N, Dubai Science Park Towers – North
P.O. Box 345002, Dubai, United Arab Emirates
(+971) 4 437-0324
info-me@phoenixcontact.com

Downloaded from Arrow.com.