





REV.	DATE	DESCRIPTION
NC	06/02/99	INITIAL RELEASE
A	10/03/07	UPDATE DRAWING FORMAT



RECOMMENDED CABLE
STRIPPING DIM'S



- NOTE:
1. CRIMPED FERRULE HEX CRIMP SIZE .128"
 2. CRIMPED CONTACT PIN - 4-WAY CRIMP OR SOLDER.

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex				
8					DRAWN	G.R.S.	10/03/07						
7					CHECKED								
6						ISSUED				PART DESCRIPTION BNC CRIMP JACK (FOR RG-178/U, 196A/U CABLE)			
5						SHEET	1 OF 1						
4	FERRULE	COPPER	NICKEL		1					PART NO. 112631			
3	CONTACT PIN	PHOS. BRONZE	GOLD		1								
2	INSULATOR	TEFLON	NATURAL		1					DWG. NO. 112631.DWG			
1	BODY	BRASS	NICKEL	1									
DESCRIPTION				MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING		CAD FILE C:/112/112631.DWG		REV. A	SIZE A	SCALE NA