

Part Number : [190070082](#)

Product Description : InsulKrimp Female Fully Insulated Quick Disconnect Flag for 12-10 AWG Wire, Tab 6.35 x 0.81mm, 94 V-0 Material, Carton

Series Number : 19007

Status : Active

Product Category : Quick Disconnects

Engineering Part Number : C-2211V



Documents and Resources

Drawings

[190070082_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[PS-19902-008-001.pdf](#)

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19007
Description	InsulKrimp Female Fully Insulated Quick Disconnect Flag for 12-10 AWG Wire, Tab 6.35 x 0.81mm, 94 V-0 Material, Carton
Product Name	InsulKrimp
Type	Flag Terminal
UPC	800756386744

Agency

UL	E79133
----	--------

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Yellow
Flammability	94V-0
Gender	Female

Glow-Wire Capable	Yes
Insulated	Fully
Insulation	Nylon (PA)
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	2.108/g
Orientation	Flag
Packaging Type	Carton
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-65° to +105°C
Wire Insulation Diameter	6.60mm
Wire Size (AWG)	10 (105 strands), 12 (65 strands)

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for AviKrimp Fully Insulated and Insulated Quick Disconnect Flags, 12-10 AWG	<u>640018800</u>

This document was generated on Apr 14, 2026