




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1680617	2016-08-03	Wes Fan	Modify Dimension.



CB-04AFMM-QL8W00
Color: Black


White Printing
白色印刷



- Note:
- * Important Dimension To Check.
 - * Working Voltage Rating: AC 300 V
 - * Working Current Rating: 10A
 - * Flame Class: UL94V-0 (UV Resistance)
 - * Waterproof Rate: IP68(Mated).
 - * Housing: Nylon+GF, Black.
 - * Male Pin: Copper Alloy, Gold Plated
 - * Cable: UL21388 16AWG*4C+AL.Mylar Black,PVC Jacket UV Resistant, OD=6.8
 - * Cable Length Tolerance: 01M:±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

CB-04AFMM-QL8DXX

XX :01~99Meters
01 :01Meter
02 :02Meters
...
99 :99Meters



Pin Assignments
Front View

4	Orange	橙
3	Red	紅
2	Brown	棕
1	Black	黑
Conn.	Wire Color	
Pin Out		

UNIT:mm		TOLERANCE ±0.5		TITLE X Lok C-Size Cable 4 Pin 10A F Conn. M Pin		Amphenol LTW		ITEM NO		DRAWN BY Wes Fan		DATE 2016-08-03	
SCALE 1:1		SIZE A4		SHEET 1 OF 1		DWG NO CB-04AFMM-QL8DXX		CHECKED BY Spring Liu		DATE 2016-08-03		APPROVED BY Kevin Hu	
REV. B		WC-REV. A.4		QC:Inspection item		CUSTOMER ALTW		APPROVED BY Kevin Hu		DATE 2016-08-03		DATE 2016-08-03	

安費諾亮泰企業股份有限公司