

BU-6162-M-XX-@

(UL® Listed, Shrouded Banana, Silicone Test Lead)



- The BU-6162-M-XX-@ is a UL® Listed, CE Certified Test Lead with Standard 4mm Shrouded Banana Plugs on both ends.
- Uses 18 AWG (413/44) UL 3577, 105°C with a highly flexible silicone jacket.
- Length is designated in inches by the “XX” in the part number.
Standard lengths are: 12”, 18”, 24”, 39”, 48”, 60” and 72”
- Material: Banana Plug – Nickel plated Beryllium Copper and Brass Cover -- Polypropylene
- Ratings:
 - o Operating Voltage: 1,000V CAT III
 - o Current: 20 Amps
 - o Operating Temperature: -40°C to 80°C
 - o Hands free testing to 3,000V
- Color: The “@” in the model number represents color. Available colors:
-0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -8 Gray, -9 White
- RoHS 3 Compliant, CE Certified

Mueller Electric Company
2850 Gilchrist Rd. Bld 5A
Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629
Phone: 330.780.2525
Fax: 330.780.2524