



Search within category

GO

BUY NOW

DESIGN / INSTALL



G1X2WH6

Panduct® type G wide slot wiring duct, 1 W x 2 H, 6' length, PVC, white.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Material	Lead-Free PVC
Color	White
Overall Length (ft.)	6
Overall Length (m)	1.8
Overall Width (In.)	1.25
Overall Width (mm)	32
Overall Height (In.)	2.12
Mount Method	Standard Mounting Holes
Cover Part Number	C1WH6
CSA Certified	Yes
UL Recognized (File No. E147128)	Yes
Length (ft.)	6.00
CE Compliant	Yes
Flammability Rating	UL94 V-0
Part Features	Wide finger and slot design provides greater rigidity and allows use with a wide range of wire and bundle sizes. Upper and lower scorelines allows easy finger and sidewall section removals.
Type	Base
UL recognized continuous use temp	122°F (50°C)
RoHS Compliancy Status	Compliant
Min. Order Qty.	6