Data sheet

BFSC M5X8 SCHLITZ

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	Mounting screw (Terminal), 5.00 mm, Steel, Depth: 8.5 mm, Width: 8.5 mm, Height: 8.5 mm
Order No.	0296700000
Type	BFSC M5X8 SCHLITZ
GTIN (EAN)	4008190881764
Qty.	100 items

Downloaded from Arrow.com.

Data sheet

BFSC M5X8 SCHLITZ

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	8.5 mm	Depth (inches)	0.3346 inch
Height	8.5 mm	Height (inches)	0.3346 inch
Width	8.5 mm	Width (inches)	0.3346 inch
Diameter	8.5 mm	Net weight	2.11 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Steel	Colour	Silver grey

System specifications

Version	for cross-connection link

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

Conductors for clamping (rated connection)

Tightening torque, max.	3 Nm	Tightening torque, min.	2 Nm

Dimensions

Diameter	8.5 mm	Metric size of the thread, external	5.00 mm

General

Installation advice	Direct mounting

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		

Downloaded from Arrow.com.