

REVISIONS	
A	CO-94361 DCS 24 NOV 99
B	207607 CSL 10 MAR 03
C	0002302 CSL 10 DEC 03

CHECK	
28AUG97	SAV
19AUG97	LJK
PTC/CAD 2D	DRAWN




MICRO SWITCH
a Honeywell Division
FED. MFG. CODE 91929

SWITCH - TOGGLE


CATALOG LISTING
32NT91-JLG SERIES CHART 1


THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CATALOG LISTING	CIRCUIT MADE WITH TOGGLE LEVER IN 			ELECTRICAL DATA
	KEYWAY SIDE (1-2, 4-5)	CENTER (1-2, 4-5)	OPPOSITE KEYWAY (2-3, 5-6)	
32NT91-1-JLG	ON	OFF	ON	L191 15A 125, <u>250</u> , 277 VAC 1/2HP 125 VAC 1HP <u>250</u> , 277 VAC 5A 125 VAC "L" 
32NT91-2-JLG	OFF	NONE	ON	
32NT91-3-JLG	ON	NONE	ON	
32NT91-21-JLG	NONE	OFF	ON	
32NT91-31-JLG	NONE	ON	ON	
32NT91-4-JLG	MOM OFF	NONE	ON	L192 10A 125, <u>250</u> , 277 VAC 1/4HP 125 VAC 1/2HP <u>250</u> , 277 VAC 3A 125 VAC "L" 
32NT91-5-JLG	MOM ON	OFF	ON	
32NT91-6-JLG	MOM ON	NONE	OFF	
32NT91-7-JLG	MOM ON	OFF	MOM ON	
32NT91-8-JLG	MOM ON	NONE	ON	
32NT91-51-JLG	NONE	ON	MOM ON	
32NT91-61-JLG	MOM ON	OFF	NONE	



- NOTES
- 1 - SWITCHES ARE CAPABLE OF WITHSTANDING A TEMPERATURE OF 160°F CONTINUOUSLY AT FULL RATED LOAD
 - 2 - MICRO SWITCH CAT. LIST. MARKED ON SIDE OF SWITCH
 -  FURNISHED UNASSEMBLED
 -  APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS
 -  BLACK FINISH



THIRD ANGLE PROJECTION	
	
SCALE	FULL
DO NOT SCALE PRINT	
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
ONE PLACE	(.0) ±.030
TWO PLACE	(.00) ±.015
THREE PLACE	(.000) ±.005
ANGLES	±
WEIGHT	

ANSI Y14.5M-1982 APPLIES