

molex

Part Number : [1301530111](#)

Product Description : Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, Flying Leads, 20A, 120V, 0.61m (2.0') Cord Length

Series Number : 130153

Status : Obsolete

Product Category : Power Distribution

Engineering Part Number : 20051-1



Documents and Resources

Drawings

[1301530111 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Obsolete
Category	Power Distribution
Series	130153
Description	Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, Flying Leads, 20A, 120V, 0.61m (2.0') Cord Length
Enclosure Rating	NEMA 4
NEMA Configuration	N/A
Product Name	Safeway
Type	GFCI Commercial Duty, Single Phase
UPC	78678828417

Agency

CSA	LR6837
UL	E66308

Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	120V AC

Physical

Cord Diameter	10.92mm (.430")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')
Cord Type	12/3 SJTW

Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Mounting Style	Portable
Net Weight	108.501/g
Number of Receptacles	0
Packaging Type	Bag
Receptacle Type	N/A

This document was generated on Jun 06, 2026

Obsolete