DXV 80 Set

Product no.: T0051318299N



Benefits

- Desoldering Iron with 80 W, 24 V for WT stations
- For removal of SMD components
- For vertical applications
- Electronically temperature controlled
- Ceramic heating element is operating wth protective low voltage
- Handle utilizes a tin collector to hold the extracted solder
- For DX soldering tips

Downloaded from Arrow.com.

Technical Data

Active Tip heating element technology	---
Power Response heating element technology	---
Silver Line heating element technology	---
Voltage	24 V
Power	80 W
Tip range	DX
Supply unit	WDD 81V, WDD 161V, WR 2, WR 3M, WR 3ME
WX-compatible	---
Temperature range °C	50 - 450
Temperature range °F	150 - 850
Heating time	65
Safety rest	WDH 40 (T0051515399)
Safety rest (optional)	WDH 40 (T0051515399)
Barrel	---
Integrated direct extraction	---

Weller Tools GmbH
Carl-Benz-Straße 2
74354 Besigheim
Germany

Phone: +49 (0) 7143 / 580-0
Fax.: +49 (0) 7143 / 580-108
Email: info@weller-tools.com
Web: www.weller-tools.com

Downloaded from Arrow.com.