

BU-P4969**(BNC Female Breakout to 20 AWG Leads)**

- The BU-P4969 is a female BNC breakout to 7" long, 20 AWG (41/36) wires which are color-coded and insulated with PVC. Wire leads are over-molded to the BNC for maximum strain relief and protection from harsh environments. The red wire is connected to the center contact pin and the black wire is connected to the shell.
- Material: BNC Body Nickel-plated brass body, tarnish resistant
 BNC Contact Gold-plated beryllium copper
- Ratings:
 - Voltage: 500 VRMS
 - Temperature: 105°C MAX
 - 15A Max Current
- RoHS compliant, 6c Exempt