



Part Number : [5054311100](#)
Product Description : Micro-Lock Plus Female Crimp Terminal, 1.25mm Pitch, 0.10µm Gold (Au) Plating, 30-26 AWG, Reel
Series Number : 505431
Status : Active
Product Category : Crimp Terminals



Documents & Resources

Drawings
[5054311100_sd.pdf](#)


3D Models and Design Files
[5054311100_stp.zip](#)

Specifications
[5054320000-AS-000.pdf](#)
[5055650000-AS-000.pdf](#)
[5054319200-200.pdf](#)
[2045321000-PS-001.pdf](#)
[5054320000-006.pdf](#)
[5054321000-PS-006.pdf](#)
[2045320000-PS-001.pdf](#)
[5055650002-000.pdf](#)
[5055651002-PS-000.pdf](#)

Tooling Specifications
[CS-505431-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33; 34
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	505431
Description	Micro-Lock Plus Female Crimp Terminal, 1.25mm Pitch, 0.10µm Gold (Au) Plating, 30-26 AWG, Reel
Application	Signal, Wire-to-Board
Product Name	Micro-Lock Plus
UPC	889056853989

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	50V AC (RMS)/DC

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	35.434/mg
Packaging Type	Reel
Plating min - Mating	0.100µm

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.78-1.02mm
Wire Size (AWG)	26, 28, 30
Wire Size mm ²	0.049-0.136

Use with Part(s)

Description	Part Number
1.25mm Pitch, Micro-Lock Plus Single Row Receptacle Housings	<u>505565</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for Micro-Lock Plus 1.25mm Pitch Wire-to-Board Receptacle Terminals, 30-26 AWG, UL1061 wire	<u>2002180300</u>
Extraction and Activation Tool	<u>638132700</u>
FineAdjust Applicator for Micro-Lock Plus, 1.25mm (.049") Wire to Board Crimp Terminal, 30-26 AWG	<u>639042300</u>

Application Tooling

Japan

Description	Part Number
S-1 Applicator for Micro-Lock Plus Terminals, 30-26 AWG	<u>5781463700</u>

This document was generated on Apr 26, 2025