



DC Hour Meters - 85093

(Home : Products : Controls and Monitoring : Monitors : DC Hour Meters : 85000)



Honeywell Hour Meter



85093_highres_85093_lowres_photo

Actual product appearance may vary.

Sales & Service

Distributor Inventory

Overview

Specs

Documentation

Rich Media

Description

With its highly reliable drive mechanism, the Honeywell 85000 Series features an odometer gear train and accurate quartz crystal timing to provide enhanced performance. UL/CSA recognized, with a variety of mounting styles. An improved odometer gear train, plus snap-together chassis, fits into a shock-proof, totally sealed case often resistant to many acids and solvents. All parts are in-process inspected. Every meter must pass a 100% function, burn-in, and timing accuracy test before shipping.

Features

- Custom CMOS integrated circuit
- Indicates operating time in hours and tenths, plus has a running indicator
- Totally sealed
- Battery system voltages: 6, 12, 24, 36, 48 60, 72, and 80 Vdc
- UL, CSA

Potential Applications

- Lawn tractors
- Garden tractors
- Farm equipment
- Gen sets
- Construction equipment
- Utility vehicles
- Industrial equipment
- Recreational vehicles
- Golf carts
- Aircraft
- Medical equipment
- Office equipment

Distributor Inventory

Input part number for stock availability

Narrow Your Search

Modify Your Search

Products

Select Option

Technology

Select Option

Industries Served

Select Option

Product Search

Product Type: All Product Types

Industry: All Industries

Search Term: Start Here ...

☐ New Products Only

☒ Entire Product Catalog

Search

My Links

- eCOM Login
- Request Access to eCOM
- Rep/AD Portal Login
- Rep/AD Portal Access Request
- Sample Request
- Digital U - HWM Learning Hub Login
- Limitless Microsite
- Supplier Microsite

Literature and Media

- Data Sheets
- Videos
- Literature
- Literature Request
- White Papers
- Application Notes
- Application Demos
- CAD Renderings

Contacts

- Customer Service
- Technical Support
- Global Sales & Service