



Representative Image

Catalog No. TC140**Description:** SADDLE SPRT MTG BASE .5X.4IN NAT NY**UPC No** 5414363058199**Home > Wire & Cable Management > Ty-Rap > Cable tie mounts**

Saddle Support Mounting Base, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 14.29mm (0.563 Inches), Width of 8.73mm (0.344 Inches), Height of 6.75mm (0.266 Inches), Mount with #4 Screw, Bulk Pack

Descriptors

Category	Cable tie mounts
Special Features	This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap
------------	--------

Dimensions

Mount Size	#4
------------	----

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	14.29 mm
Length	0.56 inch
Width	8.73 mm
Width	0.34 inch
Height	6.75 mm
Height	0.27 inch
Type of fastening	Other

by ABB

ETIM	EC000449 Mounting base and -element for cable ties
Material	Plastic
Material quality	Polyamide (PA)
Colour	Natural colour