

## 3-Breaker Maintenance Bypass Panel for 60kVA UPS S3M50K, S3M60K, SV60K and SU60K

MODEL NUMBER: **SU60KMBPK**



### Highlights

- Wall-mount manual bypass panel isolates UPS from connected loads for maintenance with no loss of network availability
- Includes Kirk-Key interlock system enhances system reliability
- 3 built-in circuit breakers, heavy-duty buswork
- Compatible with select 3-phase UPS systems

### Description

Wall-mount three-breaker manual bypass panel with Kirk-Key interlock system isolates the UPS from connected loads for maintenance with no loss of network availability. 225A breaker with KAIC rating of 65. Key included. Compatible with S3M50K, S3M60K, SV60K and SU60K models.

### Features

- Wall-mount 3-breaker manual bypass panel with Kirk Key interlock system
- Isolates the UPS from connected loads for maintenance with no loss of network availability
- 225A breaker with KAIC rating of 65
- Key included
- Compatible with S3M50K, S3M60K, SV60K and SU60K models

## Specifications

| OVERVIEW                           |                 |
|------------------------------------|-----------------|
| UPC Code                           | 037332146281    |
| Accessory Type                     | Bypass Panel    |
| Accessory Class                    | UPS Accessories |
| INPUT                              |                 |
| Nominal Input Voltage(s) Supported | 240V AC         |
| Voltage Compatibility (VAC)        | 240             |
| PHYSICAL                           |                 |
| Form Factors Supported             | Wallmount       |



Powering Business Worldwide



|                                     |                          |
|-------------------------------------|--------------------------|
| Shipping Dimensions (hwd / in.)     | 30.50 x 12.00 x 43.00    |
| Shipping Dimensions (hwd / cm)      | 77.47 x 30.48 x 109.22   |
| Shipping Weight (lbs.)              | 225.00                   |
| Shipping Weight (kg)                | 102.06                   |
| Unit Dimensions (hwd / in.)         | 42.360 x 30.120 x 11.750 |
| Unit Dimensions (hwd / cm)          | 107.6 x 76.5 x 29.8      |
| Unit Weight (lbs.)                  | 220                      |
| Unit Weight (kg)                    | 99.79                    |
| STANDARDS & COMPLIANCE              |                          |
| Product Compliance                  | RoHS                     |
| WARRANTY & SUPPORT                  |                          |
| Product Warranty Period (Worldwide) | 2-year limited warranty  |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.