





A-A
2:1



Nr no	Artikel-Nr. part no.	LP-Dicke pcb-thickness	Kontaktlänge contact length	a±0,1
1	09 23 000 9960.00	3,0 ±0,4	20,0 ±0,3	11,75
2	09 23 000 9961.00	4,0 ±0,4	20,0 ±0,3	10,7
3	09 23 000 9962.00	1,6 ±0,4	17,0 ±0,3	9,9
		4,8 ±0,4	20,0 ±0,3	
4	09 23 000 9963.00	2,4 ±0,4	17,0 ±0,3	9,1
		5,6 ±0,4	20,0 ±0,3	
5	09 23 000 9964.00	3,2 ±0,4	17,0 ±0,3	8,3
		6,4 ±0,4	20,0 ±0,3	
6	09 23 000 9965.00	4,0 ±0,4	17,0 ±0,3	7,5
		7,2 ±0,4	20,0 ±0,3	
7	09 23 000 9966.00	1,6 ±0,4	13,2 ±0,3	6,7
		4,8 ±0,4	17,0 ±0,3	
8	09 23 000 9967.00	2,4 ±0,4	13,2 ±0,3	5,9
		5,6 ±0,4	17,0 ±0,3	
9	09 23 000 9968.00	3,2 ±0,4	13,2 ±0,3	5,1
		6,4 ±0,4	17,0 ±0,3	
10	09 23 000 9969.00	4,0 ±0,4	13,2 ±0,3	4,3

 All Dimensions in mm Original Size DIN A 3			Techn. Character.				Nicht tolerierte Maß/Free size tolerances				
				Dat.	Name	Maßstab/Scale 1 : 1	DIN signal type 2C/2R shroud screw-fix				
			Detail.	06.04.06	Ge.						
			Insp.	06.04.06	Ge.						
			Stand.								
33866	28.08.06	LehT	HARTING Electronics GmbH & Co. KG					TB 09 23 000 996x			
31221			D-32339 ESPELKAMP								
Mod.	Dat.	Name					Sub.	Blatt/ page /			