

High-Speed HDMI Cable, Digital Video with Audio, 4K (M/M), Red Connectors, 3 ft. (0.91 m)

MODEL NUMBER: P568-003-RD



High-speed premium cable connects two Ultra HD HDMI-enabled devices, including computers, Blu-ray™ players, video game systems, DVRs, video cameras, A/V receivers, monitors, projectors and televisions.

Features

Connects HDMI Source to 4K TV, Projector or Monitor

- Ideal for digital signage, video presentations, point-of-sale displays, classrooms and other applications that display Ultra High Resolution (UHD) video and multi-channel audio

High Performance and Wide Compatibility

- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K), including 1080p
- Supports data transfer speeds up to 18 Gbps—the fastest bandwidth currently available over HDMI
- Supports iPad2 video mirroring when used with Apple digital AV adapter
- Backward compatible with previous HDMI generations

Superior Quality Ensures a Flawless Signal

- Corrosion-resistant gold-plated red connectors for optimal signal transfer
- Fully molded 30 AWG construction with integral strain relief for durability and long life
- Premium foil and braid shielding for EMI/RFI noise protection
- Flexible PVC jacket easy to install in tight spaces

Specifications

OVERVIEW	
UPC Code	037332196989
Technology	HDMI
Cable Type	Passive

Highlights

- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K)
- Supports data transfer speeds up to 18 Gbps
- Backward compatible with previous HDMI generations
- Premium foil and braid shielding protects against EMI/RFI noise
- Gold-plated red connectors for optimal signal transfer

Package Includes

- P568-003-RD High-Speed HDMI Cable with Digital Video and Audio (M/M), Red, 3 ft.

VIDEO	
Max Supported Video Resolution	3840 x 2160 @ 30Hz
Max Supported Color Depth	48-bit Deep Color
HDR Support	No
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
EDID Support	Yes
Signal Transmission	Bidirectional
Bandwidth	10.2 Gbps
AUDIO	
Audio Specification	ARC
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
Connector Plating	Gold
Contact Plating	Gold
Connector Style	Straight
Latching or Gripping Connector	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	0
PHYSICAL	
Color	Red
Material of Construction	ABS
Cable Jacket Color	Black
Connector Color	Red
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	6.0mm
Wire Gauge (AWG)	30
Cable Length (ft.)	3
Cable Length (m)	0.91
Ferrite Core	No
Minimum Bend Radius	30mm



Powering Business Worldwide



Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.15
Shipping Weight (kg)	0.07
ENVIRONMENTAL	
Operating Temperature Range	14 to 122 F (-10 to 50 C)
Storage Temperature Range	5 to 140 F (-15 to 60 C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
COMMUNICATIONS	
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	Yes
FEATURES & SPECIFICATIONS	
EMI/RFI Line Noise Protection	No
MST Support	No
Antibacterial	No
IP68 Rated	No
Armored Cable	No
Ethernet Support	No
HDCP Specification	1.4; 2.2
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.