

AMPHENOL RF PART NUMBER

031-30231-45

Triax BNC Clamp Plug

FIND STOCK & BUY NOW

Amphenol® RF



PRODUCT IMAGE
COMING SOON

ADD TO COMPARE

ADD TO PART LIST

PRODUCT OVERVIEW



RF Connector, Triax BNC Clamp Plug

Product Type [Connectors](#)
Product Series [Triax](#)
Status [Active](#)

DOWNLOADS



Please [contact us](#) for additional product information.

PRODUCT SPECIFICATIONS



Brand	Amphenol RF
Gender	Plug
Orientation	Straight
Termination Style	Cable - Clamp
Impedance (Ohms)	Non-Constant
Body Finish	Nickel
Body Material	Brass
Contact Finish	Gold
Contact Material	Brass
Contact Termination Style	Solder
Insulator Material	PTFE
Cable Group	Special
Coupling Mechanism	Bayonet
Max Frequency (GHz)	0.5
Polarity	Standard
Min. Temp. (Celsius)	-65
Max. Temp. (Celsius)	165
Mating Cycles	500

PRODUCT COMPLIANCE



Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C - View Certificate
-------------	--

Additional compliance information is available in our [Product Compliance Center](#).



[LOCATIONS](#)

[CAREERS](#)

[CAPABILITIES](#)

[QUALITY](#)

[PRODUCT COMPLIANCE](#)

[LITERATURE](#)

[EXTRANET LOG-IN](#)

[DISTRIBUTOR LISTING](#)

NEWSLETTER

Enter your email adress...

SUBMIT

By submitting your email, you are agreeing to receive occasional updates from Amphenol RF.

Copyright © 2018 Amphenol RF. All Rights Reserved.

[Copyright](#) | [Terms & Conditions](#) | [User Agreement](#) | [Privacy Policy](#) | [Logos](#) | [Amphenol.com](#)

LMR® is a registered trademark of Times Microwave Systems