

Specifications

Eaton MPI4012V2-R68-R



Eaton MPI40-V2, 0.68 μ H, 4.5 A Irms, 6.7 A ISAT, 33.5 m Ω resistance, SMT mounting, Iron Powder, 2-pins, 3000 qty.

Photo is representative



General specifications

PRODUCT NAME	Eaton MPI inductor
CATALOG NUMBER	MPI4012V2-R68-R
UPC	051712686853
PRODUCT LENGTH/DEPTH	4.4 mm
PRODUCT HEIGHT	1 mm
PRODUCT WIDTH	4 mm
PRODUCT WEIGHT	0.11 g
COMPLIANCES	RoHS Compliant

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	4.5 A
ISAT	6.7 A
PACKAGE QUANTITY	3000
MATERIAL	Iron powder
AUTOMOTIVE GRADE	No
FREQUENCY RATING	Greater than 9.5MHz
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-55 to 125 °C
RESISTANCE	33.5 mΩ
SIZE	4.75x4.45x1.2mm
TERMINALS	2 Pads
FRAME SIZE	4.75x4.45x1.2mm
SERIES	MPI40-V2

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - MPI4012V2-R68-R](#)

[Eaton MPI40-V2 miniature power inductors data sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

