Part Number : 1300600068
Product Description : Mini-Change MPIS, 3 Pole, 8 Ports, Straight Wiring, Yellow Housing
Series Number : 130060
Status : Active
Product Category : Passive Distribution Boxes
Engineering Part Number : ACAUX8000



Documents and Resources

Drawings

1300600068_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Passive Distribution Boxes
Series	130060
Description	Mini-Change MPIS, 3 Pole, 8 Ports, Straight Wiring, Yellow Housing
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Mini-Change
UPC	78172501464

Agency

UL	E152210

Electrical

Current - Maximum per Contact	13.0A
Functional Wiring	Parallel
Voltage - Maximum	600V AC/DC
Wiring Configuration	Single I/O per Port

Physical

Bus I/O	Mini-Change
Cable Connector Orientation	Straight
Cable Length	N/A
Home Run Cable Length	N/A
Home Run Connector	Mini-Change - 3 pole
Home Run Interface	N/A
Keyway	Single

Downloaded from Arrow.com.

LED Indicator	None
Material - Cable Jacket	N/A
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	835.062/g
Orientation	Side Mount
Poles	3
Poles (wired)	3
Ports	8
Temperature Range - Operating	0° to +60°C

Downloaded from Arrow.com.