



APCA00060645220M00

Search by :

Part Number

Characteristics

Cross reference



MP Auto ?

SMD Shielded Type
Wire-winding Process & Ultra High Current

Series Pdf

Product detail	
L(mm) ±	6.0±0.2
W(mm) ±	6.3±0.2
T(mm) ±	4.5±0.3
Inductance(uH)	22
Tolerance(±%)	20
Test Frequency	100kHz,1V
RDC(Ω)Max	0.09
Isat(A)Typ	1.4
Isat(A)Max	1.1
Irms(A)	1.8
Operating Temperature	−40℃~125℃(Including self - temperature rise)

[Media Center](#)

[New Products](#)

[Events](#)

[Product Notices](#)

Contact Us

[Contact Info](#)

[Contact Form](#)

[Join Chilisín](#)

[Terms of Use](#)

[Privacy policy](#)

[Sitemap](#)



Inductor



Resistor



Powder

Copyrights © 2018. Chilisín. All rights reserved.