

Product data sheet

Specifications



APC IT Power Distribution Module 3 Pole 5 Wire 20A 240V IEC309 140cm

PDM3520IEC309-140

⚠ Discontinued

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Ships within 3 Weeks

Main

Main Input Voltage	230 V
Main Output Voltage	240 V
Input Connection Type	IEC 60309
Provided equipment	Installation guide

Physical

Colour	Grey
Height	12.7 cm
Width	44.4 cm
Depth	40.6 cm
Net weight	3.55 kg

Input

Network frequency	60 Hz
Permissible voltage	200...240 V
Max line current	20 A

Output

Max current draw	20 A
Number of power socket outlets	1 IEC 309

Conformance

Product certifications	UL listed
------------------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Recommended replacement(s)