
HellermannTyton

Technical data sheet

Article number:
111-02901 T30XL



Product Group	Cable Ties Polyamide 6.6 standard
Product Family	T-Series in PA66 black
Material	Polyamide 6.6 (PA66)
Colour	Black (BK)

Application Tool	ProCut 9 no battery, MK3PNSP2, EVOcut, MK7P, MK9P, MK9P w/ Upper air, MK10-SB, MK20, MK21, EVO7, EVO7SP, EVO7i, EVO7iSP, EVO9SP, EVO9HT, EVO9i, EVO9iSP, EVO9iHT
Bundle Diameter max (metric)	105.0 mm
Bundle Ø min.	1.5 mm
Flammability	UL 94 V2
Halogen-free	Yes
Length (L)	365.0 mm
Min.Tensile Strength	135 N
Operating Temperature	-40 °C to +85 °C
Package Content packed in	bag
Pack Cont.	100 pcs.
Releasable Closure (Yes/No)	No
Specifications	UL 62275
Toothing (Serration)	Inside Serrated
UL-File Number	E64139
Variant	Inside Serrated
Width (W)	3.6 mm

HF RoHS

created on 6. September 2024, 5:30 pm

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.