



Home > 3045-B-632-B



Swage Standoffs

Model: 3045-B-632-B

Select Finish

-0 No Plate

Request Quote

[Request Custom Part](#)

RFQ

Choose a CAD format

Download CAD

View 3D Model

View 2D Drawing

Product Details

These standoffs are made of Brass. They are Round shaped with diameter as 1/4". The thread for this part is 6-32 and length is 1/8".

SWAGE TOOLING

±.003	S	P
.075	A	1/32
.105	B	1/16
.135	C	3/32
.165	D	1/8
.230	E	3/16
.290	F	1/4

Thread	6-32
O.D.	1/4"
Shape	Round
Length (L)	1/8"
Material	Brass
RoHS	Yes
Shank Length	0.105"
Board Thickness	1/16"
Shank Diameter	0.188"
Thread Clearance	0.150"
Finish	-0 No Plate



TECHNICAL INFORMATION

Electronic Hardware Components
Engineering Data

COMPANY

RAF Quality Management
Industry Links