

[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)

[Home](#) / [Products](#) / [FLOS & FLOS+](#) / [Y Series B Size](#)

Product Line

[Single Pair Ethernet](#) >[ZConnect](#) >[Ceres](#) >[X-Lok](#) >[M Series](#) >[FLOS & FLOS+](#) >[Accessory](#)[B Series A Size](#)[B Series B Size](#)[B Series C Size](#)[B Series D Size](#)[K Series B Size](#)[K Series C Size](#)[K Series D Size](#)[Y Series B Size](#)[Power](#) >[RBL](#) >[HS-Lok](#) >[NM51-0000](#)[Heavy Duty Shielded](#) >[RJ](#) >[USB](#) >[SSL](#) >[HDMI](#) >[DVI](#) >[Fiber Optic](#) >[RF](#) >[Cable Joiner](#) >[Cable Gland](#) >[Pressure Relief Vent](#) >[LED Light Guide](#) >[D-Sub](#) >

FDYB-09FGMS-NDK-000

Operating Temperature: -40°C ~ +125°C

Transmission Speed: N/A

Shielded: Metal, Shielded

Jacket Material: N/A

Certificate: N/A

You must login first for view the price

Quantity

- 1 +

Check Stock

Add to Cart

Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search



FLOS, Y Series B Size,...
FDYB-09555B-NDK-001

- 0 +



Add to Cart

Inquiry

ABOUT AMPHENOL LTW

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK

Specifications

Download / CAD

Nominal Current

5A

Connector Type

Field Installable

Shielded

Metal, Shielded

No. of Contacts

09

Connector Gender

Male

Backshell

Straight

Mating Style

Push Pull

IP Rating

IPX8

Assembly Style

Solder

[More Options](#)

People Also Bought

