

Certified Peripherals / Products / Flash Card / Apacer 128M CF Card I-grd with Common Temperature and Non-removable Setting /

- Certified Peripherals
- Products
- Solution
- Partnership
- Procurement Service
- CPU and Memory Finder



96FMCFI-128-CT-AP2



- Datasheet (PDF)
- Testing Report (PDF)
- Get Price

Product Spec

Product	96FMCFI-128-CT-AP2
Product Description	Apacer 128M CF Card I-grd with Common Temperature and Non-removable Setting
Manufacturer	APACER
Capacity	128M
Reading Transfer Rate	35MB/S
Writing Transfer Rate	25MB/S
Operating Temperature	0 - 70C
DMA Mode	DMA
Disk Mode	FIXED MODE
MTBF	2,000,000 HOURS
RoHS Status	YES
EOL	Q2 / 2014

ADVANTECH Online

Buy OnlineLive Chat1-888-576-9668

- Contact Us

Price and Quotation

RMA Service

Technical Support

Worldwide Offices
- Global eStore

eStore

Warranty Policy
- Popular Links

Advantech TALKs

MyAdvantech Magazine

Worldwide Events

Solution Day
- About Advantech

Company Information

Investor Relations

Job Opportunities

Citizenship Programs