



Part Number : [1300980123](#)
Product Description : MAX-LOC Strain Relief Cord-
Sealing Grip, 3/4" NPT, 90° Angle Male, Cable
Diameter 15.88-19.05mm (.625-.750")
Series Number : 130098
Status : Active
Product Category : Cable Grips
Engineering Number : 5543



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, 90° Angle Male, Cable Diameter 15.88-19.05mm (.625-.750")
NEMA Rating	NEMA 3R
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678872166

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	90° Angle
Cable Diameter	15.88-19.05mm (.625-.750")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Net Weight	1.000/g
Number of Holes	1
O-Ring	No
Thread Size	3/4" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 3/4" NPT	<u>1300990144</u>
MAX-LOC Gasket Sealing Ring, 3/4" NPT, Black	<u>1300990150</u>
MAX-LOC O-Ring, 3/4" NPT	<u>1301800333</u>

This document was generated on Sep 18, 2025