

Plug socket module USA/Japan (NEMA 5-15)



Image is for illustration purposes only. Please refer to product description.

Part number	39 50 001 0004
Specification	Plug socket module USA/Japan (NEMA 5-15)
HARTING eCatalogue	https://b2b.harting.com/39500010004

Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Socket
Specification	Finger safe

Version

Termination method	Screw termination
Field of application	USA Japan

Termination data

Supply voltage	125 V AC
Nominal current	15 A
Nominal frequency	60 Hz

Technical characteristics

Conductor cross-section	2.5 mm²
Mounting depth	30 mm

Material properties

Material (hood/housing)	Thermoplastic
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide

Commercial data

Packaging size	1
Net weight	4.333 g
Country of origin	Hungary
European customs tariff number	85366990
GTIN	5713140154896
ETIM	EC000450
eCl@ss	27144042 Plug socket